



Übersicht PKD Fräser 6C Tools AG

Stand: September 2019

Artikel	D ₁	L ₂	L ₁	D ₂	R				Z	KSM
					0.05	0.1	0.2	0.3		
					-005	-010	-020	-030		
TM-P-1105-030-xxx	0.3	0.5	-	-	●	-	-	-	3	●
TM-P-1105-035-xxx	0.35	0.5	-	-	●	-	-	-	3	●
TM-P-1105-040-xxx	0.4	0.5	-	-	●	-	-	-	3	●
TM-P-1105-050-xxx	0.5	0.5	-	-	●				4	●
TM-P-1110-050-xxx		1.0	-	-	●					
TM-P-1115-050-xxx		1.5	-	-	●					
TM-P-1105-060-xxx	0.6	0.5	-	-	●				5	●
TM-P-1110-060-xxx		1.0	-	-	●					
TM-P-1115-060-xxx		1.5	-	-	●					
TM-P-1105-070-xxx	0.7	0.5	-	-	●				6	●
TM-P-1110-070-xxx		1.0	-	-	●					
TM-P-1115-070-xxx		1.5	-	-	●					
TM-P-1130-070-xxx		3.0	1.8	0.6	●					
TM-P-1105-080-xxx	0.8	0.5	-	-	●	-			6	●
TM-P-1110-080-xxx		1.0	-	-	●	-				
TM-P-1115-080-xxx		1.5	-	-	●	●				
TM-P-1130-080-xxx		3.0	1.8	0.7	●	●				
TM-P-1105-090-xxx	0.9	0.5	-	-	●	-			7	●
TM-P-1110-090-xxx		1.0	-	-	●	-				
TM-P-1115-090-xxx		1.5	-	-	●	●				
TM-P-1130-090-xxx		3.0	1.8	0.8	●	●				
TM-P-1105-100-xxx	1.0	0.5	-	-	●	-	-		7	●
TM-P-1110-100-xxx		1.0	-	-	●	-	-			
TM-P-1115-100-xxx		1.5	-	-	●	●	●			
TM-P-1130-100-xxx		3.0	1.8	0.9	●	●	●			
TM-P-1150-100-xxx		5.0	1.8	0.9	●	●	●			
TM-P-1110-110-xxx	1.1	1.0	-	-	●	-	-		7	●
TM-P-1115-110-xxx		1.5	-	-	●	●	●			
TM-P-1130-110-xxx		3.0	1.8	1.0	●	●	●			
TM-P-1150-110-xxx		5.0	1.8	1.0	●	●	●			
TM-P-1110-120-xxx	1.2	1.0	-	-	●	-	-	-	9	●
TM-P-1115-120-xxx		1.5	-	-	●	●	●	●		
TM-P-1130-120-xxx		3.0	1.8	1.1	●	●	●	●		
TM-P-1150-120-xxx		5.0	1.8	1.1	●	●	●	●		

Beispiel: Fräser D=1.0mm, L=3mm, R=0.2mm → TM-P-1130-100-020

